### 3-channel palm-sized electroacupuncture

# **E**\$=130

For busy clinics that require multiple units

Well suited for out of office use

Low/High intensity settings

Built in battery checker









#### **Features**

- High Performance and Versatility
  - Low/High intensity settings
  - Frequency selector offers a complete frequency range (1–500Hz)
  - Suitable for needles
- Unique Wave Form
  - Unique wave pulse minimizes excessive charge build up in the tissue and damaging the nerve
- Safe, Reliable, and Easy to Use
  - Each of the 3 channels are independently controlled
  - Special dial controls allow easy use yet safe operation
  - Built in battery life check with indicator light



#### **Specifications**

Power supply: One 9 V battery

Frequency: 1–500 Hz, variable

**Maximum output voltage:** 30 V  $\pm$  15% (at 500 $\Omega$  laod)

**Current amplitude (max.):**  $14 \text{ mA} \pm 20\%$  (rms, at  $500\Omega$  laod)

Phase duration: 100 µs Number of channel: 3 Others: Battery checker

Pulse rate indication

Safety class: Internally powered equipment

Type BF (IEC), Class IIa (MDD)

**Dimensions:** 63 (W)  $\times$  96 (H)  $\times$  27 (D) mm

Weight: 120 gr. (excluding battery)

#### **Ordering Data**

## Standard Kit

ES-130 complete with standard accessories, including

1 × 260182 Carrying bag

 $1 \times 180432$  Electrode cable (white)  $1 \times 180433$  Electrode cable (yellow)

1 × 180434 Electrode cable (green)



\*Designs and specifications are subject to change without notice.



3-3-3 Toyotama-Minami, Nerima-ku, Tokyo 176-0014, Japan TEL:81-3-3994-4619 FAX:81-3-3994-1465 URL: http://www.itolator.co.jp/english/ E-Mail: itocoltd@itolator.co.jp

